

WIL-AXXXX-FXSF-5700-X800-GST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	2979350000
Type	WIL-AXXXX-FXSF-5700-X800-GST
GTIN (EAN)	4099986832794
Qty.	1 items

WIL-AXXXX-FXSF-5700-X800-GST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	135 mm	Depth (inches)	5.3149 inch
Height	38 mm	Height (inches)	1.4961 inch
Width	816 mm	Width (inches)	32.1259 inch
Net weight	300 g		

Temperatures

Operating temperature	-20 - 45°C
-----------------------	------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	60b0f8b3-d5d4-4f2d-a3c8-d2f055e5e550

Cable technical specifications

Housing main material	hard anodised aluminium
-----------------------	-------------------------

Connection data

Number of poles	3
-----------------	---

Electric data

Rated voltage	230 V AC	Power	32.5 W
Dimmable	yes, stepless dimming		

General technical data

Light colour (CCT)	5700K, White	Light current	5825 lm
Emitting angle	100 °	Operating life	60.000 h
Type of mounting	Screw mounting	Protection degree	IP40

Material data

Housing main material	hard anodised aluminium
-----------------------	-------------------------

Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		