

HDC MDSUB 9 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

| | |
|------------|--------------------------------|
| Order No. | 2984100000 |
| Type | HDC MDSUB 9 MC |
| GTIN (EAN) | 4099986842892 |
| Qty. | 1 items |

HDC MDSUB 9 MC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 14.6 mm | Depth (inches) | 0.5748 inch |
| Height | 35.2 mm | Height (inches) | 1.3858 inch |
| Width | 34.2 mm | Width (inches) | 1.3465 inch |
| Net weight | 162 g | | |

General data

| | | | |
|------------------------------|---------------|--------------------------------------|----------|
| Number of poles | 9 | UL 94 flammability rating | V-0 |
| Plugging cycles | ≥ 500 | Type | Male |
| Surge voltage category | III | Pollution severity | 3 |
| Basic material | Polycarbonate | Series | ModuPlug |
| Rated voltage (DIN EN 61984) | 48 V | Rated impulse voltage (DIN EN 61984) | 0.8 kV |
| Rated current (DIN EN 61984) | 1 A | | |

Version

| | | | |
|------------------------------------|----------------------|-------------------------------|---------------------|
| Stripping length, rated connection | 4.2 mm | Conductor cross-section, max. | 0.5 mm ² |
| Conductor cross-section, min. | 0.08 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000438 | ETIM 9.0 | EC000438 |
| ETIM 10.0 | EC000438 | ECLASS 14.0 | 27-44-02-17 |
| ECLASS 15.0 | 27-44-02-17 | | |

