

H0,5/8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Order No.	2984690000
Type	H0,5/8
GTIN (EAN)	4099986845992
Qty.	1000 items
Packaging	loose

H0,5/8

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

Dimensions and weights

Height	8 mm	Height (inches)	0.315 inch
Diameter	0.5 mm	Net weight	0.04 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Wire-end ferrules

Contact surface diameter (D1)	1 mm	Contact surface length (L2)	8 mm
Collar diameter (D2)	2.1 mm	L1 in mm	8.00 mm
Wire connection cross section AWG, max.	AWG 20	Stripping length	8 mm
Conductor cross-section	0.5 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		