

## H0,5/8

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

### General ordering data

Order No.	2984690000
Type	<a href="#">H0,5/8</a>
GTIN (EAN)	4099986845992
Qty.	1000 items
Packaging	loose

**H0,5/8**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

**Dimensions and weights**

Height	8 mm	Height (inches)	0.315 inch
Diameter	0.5 mm	Net weight	0.04 g

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Wire-end ferrules**

Contact surface diameter (D1)	1 mm	Contact surface length (L2)	8 mm
Collar diameter (D2)	2.1 mm	L1 in mm	8.00 mm
Wire connection cross section AWG, max.	AWG 20	Stripping length	8 mm
Conductor cross-section	0.5 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		