

**KT 40****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

**General ordering data**

Version	Cutting tools
Order No.	<a href="#">2993490000</a>
Type	KT 40
GTIN (EAN)	4099986874312
Qty.	1 items

## KT 40

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	37 mm	Depth (inches)	1.4567 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	305 mm	Width (inches)	12.0078 inch
Net weight	808.72 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

### Cutting tools

Copper sector cable	3 x 50 SM	Copper cable - flexible, max. (kcmil)	500 kcmil
Copper cable - flexible, max.	300 mm <sup>2</sup>	Copper cable - stranded, max. (kcmil)	600 kcmil
Copper cable - stranded, max.	300 mm <sup>2</sup>	Copper cable, max. diameter	40 mm
Aluminium sector cable	4 x 50 SE	Stranded aluminium cable, max. (kcmil)	500 kcmil
Stranded aluminium cable, max (mm <sup>2</sup> )	300 mm <sup>2</sup>	Stranded aluminium cable, max. diameter	40 mm

### Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		