

KT 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tools
Order No.	2993490000
Type	KT 40
GTIN (EAN)	4099986874312
Qty.	1 items

KT 40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	37 mm	Depth (inches)	1.4567 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	305 mm	Width (inches)	12.0078 inch
Net weight	808.72 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Cutting tools

Copper sector cable	3 x 50 SM	Copper cable - flexible, max. (kcmil)	500 kcmil
Copper cable - flexible, max.	300 mm ²	Copper cable - stranded, max. (kcmil)	600 kcmil
Copper cable - stranded, max.	300 mm ²	Copper cable, max. diameter	40 mm
Aluminium sector cable	4 x 50 SE	Stranded aluminium cable, max. (kcmil)	500 kcmil
Stranded aluminium cable, max (mm ²)	300 mm ²	Stranded aluminium cable, max. diameter	40 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		