

KT 50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tools
Order No.	2993500000
Type	KT 50
GTIN (EAN)	4099986874329
Qty.	1 items

KT 50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.5748 inch
Height	110 mm	Height (inches)	4.3307 inch
Width	345 mm	Width (inches)	13.5826 inch
Net weight	1205.6 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Cutting tools

Copper sector cable	4 x 70 SM	Copper cable - flexible, max. (kcmil)	800 kcmil
Copper cable - flexible, max.	400 mm ²	Copper cable - stranded, max. (kcmil)	800 kcmil
Copper cable - stranded, max.	400 mm ²	Copper cable, max. diameter	52 mm
Aluminium sector cable	4 x 70 SE	Stranded aluminium cable, max. (kcmil)	800 kcmil
Stranded aluminium cable, max (mm ²)	400 mm ²	Stranded aluminium cable, max. diameter	52 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		