

**KT 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

**General ordering data**

Version	Cutting tools
Order No.	<a href="#">2993500000</a>
Type	KT 50
GTIN (EAN)	4099986874329
Qty.	1 items

**KT 50**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.5748 inch
Height	110 mm	Height (inches)	4.3307 inch
Width	345 mm	Width (inches)	13.5826 inch
Net weight	1205.6 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Cutting tools**

Copper sector cable	4 x 70 SM	Copper cable - flexible, max. (kcmil)	800 kcmil
Copper cable - flexible, max.	400 mm <sup>2</sup>	Copper cable - stranded, max. (kcmil)	800 kcmil
Copper cable - stranded, max.	400 mm <sup>2</sup>	Copper cable, max. diameter	52 mm
Aluminium sector cable	4 x 70 SE	Stranded aluminium cable, max. (kcmil)	800 kcmil
Stranded aluminium cable, max (mm <sup>2</sup> )	400 mm <sup>2</sup>	Stranded aluminium cable, max. diameter	52 mm

**Classifications**

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		