

HDC 10B TSBU 1M25G EXI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The option of disconnecting cables in the EXI area simplifies installation and servicing and enables better preparation.

The Rockstar® EXI enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue EXI gland is required to complete the enclosure.

General ordering data

Version	HDC enclosures, Installation size: 4, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
Order No.	3001370000
Type	HDC 10B TSBU 1M25G EXI
GTIN (EAN)	4099986902442
Qty.	1 items

HDC 10B TSB 1M25G EXI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals	CE
ROHS	Conform

Dimensions and weights

Depth	73 mm	Depth (inches)	2.874 inch
Height	52 mm	Height (inches)	2.0472 inch
Width	58.5 mm	Width (inches)	2.3031 inch
Net weight	141 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Dimensions

Cable entry	w. thread	Width housing C	43 mm
Total length housing	73 mm	Height of housing B	52 mm

General data

Tightening torque	1.2 Nm	Housing main material	diecast aluminium
Surface finish	Powder coating	Protection degree	IP65, in plugged condition
EMC housings	No	Material of locking element	Stainless steel, rust-proof
Explosion protection type	II 2G Ex ib IIC T6 Gb		

Version

Size of cable entries	M 25	Top part/bottom part/lid	upper part
Tightening torque	1.2 Nm	Number of cable entry sideways	1
Design of housing	Cable entry from side, Plug housing	Design of locking system	Side-locking clamp on lower side
Design	Standard	Installation size	4
Cable entry	w. thread	Type	Plug
Clamp version	Side-locking clamp	Internal thread	M 25
Colour (RAL)	RAL 7035	BG	4
Suitable for ModuPlug®	No		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 10B TSBU 1M25G EXI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmuller.com

Accessories

Chloroprene seal material, -40°C - +70°C




Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety). Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

General ordering data

Type	VG M25 EXI 12-17 CR7J G4	Version
Order No.	2722270000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 25,
GTIN (EAN)	4050118821505	10 mm, OD min. 12 - OD max. 17 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	50 ST	(30 min.), Polyamide 6
Type	VG M25 EXI 14-18 CR7J G4	Version
Order No.	2722280000	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 25,
GTIN (EAN)	4050118821512	10 mm, OD min. 14 - OD max. 18 mm, IP54, IP66, IP67, IP68 - 5 bar
Qty.	25 ST	(30 min.), Polyamide 6

Size 4



The ability to disconnect cables in the EXI area simplifies installation and service and enables better preparation. The Rockstar® EXI inserts shown here are equipped with PUSH IN connections and are therefore very easy to connect. They are identified by the article designation

General ordering data

Type	HDC HE 10 FP EXI	Version
Order No.	3001220000	, Female, 500 V, 5 A, Number of poles: 10, PUSH IN, Installation size:
GTIN (EAN)	4099986902329	4
Qty.	1 ST	
Type	HDC HE 10 MP EXI	Version
Order No.	3001230000	, Male, 500 V, 5 A, Number of poles: 10, PUSH IN, Installation size: 4
GTIN (EAN)	4099986902336	
Qty.	1 ST	