

## CMA-A20-60-1A-1-1VA

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Plug-on current transformers

Plug-on current transformers are used wherever high currents of up to 5000A need to be measured and processed. Our plug-on current transformers supply secondary currents of 1A or 5A. Weidmüller also offers compact low-power current transformers to convert currents of up to 600 A to voltages of up to 333 mV.

### General ordering data

|              |  |
|--------------|--|
| Version      | Primary current: 60 A, Secondary current max.: 1 A, Load: 1 VA, Tolerance class: 1 |
| Order No.    | <a href="#">3008210000</a>   |
| Type         | CMA-A20-60-1A-1-1VA  |
| GTIN (EAN)   | 4099986909465  |
| Qty.         | 1 items  |
| Manufacturer | ENTES Elektronik   |

## CMA-A20-60-1A-1-1VA

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 57 mm | Depth (inches)  | 2.2441 inch |
| Height     | 65 mm | Height (inches) | 2.5591 inch |
| Width      | 47 mm | Width (inches)  | 1.8504 inch |
| Net weight | 250 g |                 |             |

### Temperatures

Storage temperature Operating temperature -5 °C...40 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

### Electrical attributes

Tolerance class 1 Secondary current 0...1 A  
 Load 1 VA Primary current 60 A

### Technical properties

Protection degree IP20 Thermal rated continuous current 1.2 x I<sub>rated</sub>  
 I<sub>thermal</sub>  
 Nominal frequency 50 / 60 Hz

### Insulation coordination

Tolerance class 1 Insulation voltage 3 kV / 1 min

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002048    | ETIM 9.0    | EC002048    |
| ETIM 10.0   | EC002048    | ECLASS 14.0 | 27-21-09-02 |
| ECLASS 15.0 | 27-21-09-02 |             |             |

CMA-A20-60-1A-1-1VA

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)

