

WIL-HXXXX-FXSF-XX89-USBC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The H series is ideal for mobile lighting of work areas. All dark areas can be illuminated thanks to the simple handling and the built-in rechargeable battery. The battery can be recharged quickly and easily using the cable supplied. The work lamp provides a mobile lighting option with up to 6500 K.

General ordering data

Order No.	3031110000
Type	WIL-HXXXX-FXSF-XX89-USBC
GTIN (EAN)	4099986975743
Qty.	1 items

WIL-HXXXX-FXSF-XX89-USBC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	17.8 mm	Depth (inches)	0.7008 inch
Height	89 mm	Height (inches)	3.5039 inch
Width	23.1 mm	Width (inches)	0.9094 inch
Net weight	40 g		

Temperatures

Operating temperature -10 - 35°C

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

Cable technical specifications

Cable Material	Polycarbonate	Housing main material	Aluminum
Cable length	0.5 m		

General technical data

Type of connection	USB C	Shape of the LED module	Round
Number of LEDs	1	Light colour (CCT)	6500K, 5000K
Luminosity	300 lm	Light current	300 lm
Emitting angle	120°	Impact resistance	IK07
Protection degree	IPX3	Efficiency class (according to EU Directive No. 874/2012)	Not required

Material data

Housing main material	Aluminum	Material of end caps	Polycarbonate
-----------------------	----------	----------------------	---------------

Classifications

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

