

**POWERCRIMPER VARIO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The rationalisation of crimping processes calls for more and more automation of the individual steps. "Optimisation of installation times" is what the markets of the future will be demanding of their strategic partners. Automatic machines that permit rational processing of conductor materials represent the answer to an approach geared to future needs. Versatility and functionality are decisive factors for the customer. With our comprehensive line of automated machinery, Weidmüller provides professional and efficient solutions for cable preparation and processing.

**General ordering data**

Version	Automatic machines, Crimping machine
Order No.	<a href="#">3032890000</a>
Type	POWERCRIMPER VARIO
GTIN (EAN)	409998698539 1
Qty.	1 items

## POWERCRIMPER VARIO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	300 mm	Depth (inches)	11.811 inch
Height	220 mm	Height (inches)	8.6614 inch
Width	190 mm	Width (inches)	7.4803 inch
Net weight	9000 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6a, 6b, 6c, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

### Automatic crimping

Drive	electrical	Pulse time	approx. 1 s
Wire end ferrules cross-section, max.	6 mm <sup>2</sup>	Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>
Crimping range, max.	6 mm <sup>2</sup>	Crimping range, min.	0.5 mm <sup>2</sup>
Crimping length	12 mm	Consumables	With and without plastic collar, loose cable lugs, for loose part insulated cable lugs
Electrical connection	100-240 V / 50/60 Hz / 100 VA	Insertion length	38 mm
Crimping range	0.5 - 6.00 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

**POWERCRIMPER VARIO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## POWERCRIMPER VARIO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### Accessories / replacement parts

#### General ordering data

Type	ADAPTER PCV HTO	Version
Order No.	<a href="#">3064900000</a>	Automatic machines, Crimping machine
GTIN (EAN)	4099987058353	
Qty.	1 ST	
Type	EINSATZPAAR PZ 16E	Version
Order No.	<a href="#">9012640000</a>	16mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4008190114831	
Qty.	1 ST	
Type	EINSATZPAAR PZ 6/5	Version
Order No.	<a href="#">9011620000</a>	6mm <sup>2</sup> , Trapezoidal crimp
GTIN (EAN)	4008190207939	
Qty.	1 ST	
Type	ERTE ES PZ ZH 16	Version
Order No.	<a href="#">9054580000</a>	
GTIN (EAN)	4032248052493	
Qty.	1 ST	
Type	STORAGEBOX PCV	Version
Order No.	<a href="#">3043810000</a>	Automatic machines, Crimping machine
GTIN (EAN)	4099987017084	
Qty.	1 ST	
Type	ADAPTER PCV HTO	Version
Order No.	<a href="#">3064900000</a>	Automatic machines, Crimping machine
GTIN (EAN)	4099987058353	
Qty.	1 ST	
Type	EINSATZPAAR PZ 16E	Version
Order No.	<a href="#">9012640000</a>	16mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4008190114831	
Qty.	1 ST	
Type	EINSATZPAAR PZ 6/5	Version
Order No.	<a href="#">9011620000</a>	6mm <sup>2</sup> , Trapezoidal crimp
GTIN (EAN)	4008190207939	
Qty.	1 ST	
Type	ERTE ES PZ ZH 16	Version
Order No.	<a href="#">9054580000</a>	
GTIN (EAN)	4032248052493	
Qty.	1 ST	
Type	STORAGEBOX PCV	Version
Order No.	<a href="#">3043810000</a>	Automatic machines, Crimping machine
GTIN (EAN)	4099987017084	
Qty.	1 ST	