

## BEP 2C 2.5N

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	B-series, End plate
Order No.	<a href="#">3040510000</a>
Type	BEP 2C 2.5N
GTIN (EAN)	4099987010184
Qty.	50 items

**BEP 2C 2.5N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	28.3 mm	Depth (inches)	1.1142 inch
Height	47.7 mm	Height (inches)	1.8779 inch
Width	2.1 mm	Width (inches)	0.0827 inch
Net weight	1.74 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	PA 66	Colour	grey
UL 94 flammability rating	V-0		

**System specifications**

Version	End plate
---------	-----------

**Additional technical data**

With snap-in pegs	Yes	Snap-on	Yes
-------------------	-----	---------	-----

**Classifications**

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		