


BEP 4C 2.5N BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	B-series, End plate
Order No.	3040560000
Type	BEP 4C 2.5N BL
GTIN (EAN)	4099987010238
Qty.	50 items

BEP 4C 2.5N BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	28.3 mm	Depth (inches)	1.1142 inch
Height	70.5 mm	Height (inches)	2.7756 inch
Width	2.1 mm	Width (inches)	0.0827 inch
Net weight	2.51 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66	Colour	blue
UL 94 flammability rating	V-0		

System specifications

Version	End plate
---------	-----------

Additional technical data

With snap-in pegs	Yes	Snap-on	Yes
-------------------	-----	---------	-----

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		