

## CXX V 72

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

Version	CUBESERIES, Protective varistor, Rated control voltage: 110...130 V AC, Plug-in connection
Order No.	<a href="#">3053480000</a>
Type	CXX V 72
GTIN (EAN)	4099987023269
Qty.	20 items

**CXX V 72**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	23 mm	Depth (inches)	0.9055 inch
Height	9.2 mm	Height (inches)	0.3622 inch
Width	12.8 mm	Width (inches)	0.5039 inch
Net weight	2 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...70 °C
Operating temperature			

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Control side**

Rated control voltage	110...130 V AC	Status indicator	No
Protective circuit	Varistor		

**General data**

Colour	black		
UL94 flammability rating component	Component	Housing	
	UL94 flammability rating	V-2	

**Connection data**

Wire connection method	Plug-in connection
------------------------	--------------------

**Classifications**

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		

**Drawings**

**Connection diagram**



**Dimensional drawing**



Miscellaneous

Type code CUBESERIES LED / protective module versions

