

MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | Klippon K (aluminium empty enclosure), Mounting plate, Mounting plate, Height: 67 mm, Width: 114 mm, Depth: 2 mm, Basic material: Sheet steel, galvanized, galvanized, silver |
| Order No. | 3073020000 |
| Type | MOPL K21 STAHL |
| GTIN (EAN) | 4008190857950 |
| Qty. | 1 items |

MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 2 mm | Depth (inches) | 0.0787 inch |
| Height | 67 mm | Height (inches) | 2.6378 inch |
| Width | 114 mm | Width (inches) | 4.4882 inch |
| Mounting dimension - height | 33.5 mm | Mounting dimension - width | 106 mm |
| Net weight | 102 g | | |

Temperatures

| | |
|-----------------------|--|
| Operating temperature | |
|-----------------------|--|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|------------|----------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |

General information on accessories

| | | | |
|----------------------------|------------|-----------------------------|-------------------------|
| Material thickness | 2 mm | Type of fixing | when screwed in |
| Surface finish | galvanized | Basic material | Sheet steel, galvanized |
| Mounting dimension - width | 106 mm | Mounting dimension - height | 33.5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ETIM 10.0 | EC000213 | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 | | |

MOPL K21 STAHL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

TS 15



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TS15X5 ST K21 | Version | |
| Order No. | 8000003886 | Rail, TS 15, Width: 114 mm, with slot, Steel, galvanic zinc plated and passivated | |
| GTIN (EAN) | 4050118627930 | | |
| Qty. | 20 ST | | |

Depth 7.5 mm



The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS 15
- Mounting plates
- Hinges
- Wall-mounted holder

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TS35X7.5 ST K21 | Version | |
| Order No. | 8000003897 | Rail, TS 35, TS 35 x 7.5, Width: 114 mm, without slot, Steel, galvanic zinc plated and passivated | |
| GTIN (EAN) | 4050118652598 | | |
| Qty. | 20 ST | | |