

HDC MMBIT 8 MC M2 SH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Data module, 48 V, 10 A, Cat. 5e, Number of poles: 8, Crimp connection, Male, Required plug-in slots: 1
Order No.	3092890000
Type	HDC MMBIT 8 MC M2 SH
GTIN (EAN)	4099987109932
Qty.	1 items

HDC MMBIT 8 MC M2 SH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	58.9 mm	Height (inches)	2.3189 inch
Width	33.8 mm	Width (inches)	1.3307 inch
Length	14.6 mm	Length (inches)	0.5748 inch
Net weight	30.4 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number of poles	8	UL 94 flammability rating	V-0
Category	Cat. 5e	Plugging cycles	≥ 500
Type	Male	Surge voltage category	III
Pollution severity	3	Basic material	Polycarbonate
Series	ModuPlug	Rated voltage (DIN EN 61984)	48 V
Rated impulse voltage (DIN EN 61984)	0.8 kV	Rated current (DIN EN 61984)	10 A
Required plug-in slots	1		

Version

Wire connection cross section AWG, max.	AWG 26	Type of connection	Crimp connection
Wire connection cross section AWG, min.	AWG 16	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.14 mm ²		

Power contact

Tightening torque, max. according to the conductor cross-section	Conductor cross-section, min.	0.14 mm ²
	Conductor cross-section, max.	1.5 mm ²

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		

HDC MMBIT 8 MC M2 SH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

