

IE-AD-3RJ12-1:1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



If you need an adapter that lets you use one 8-core installation cable for two 4-core services, then the Weidmüller cable splitter module is the right choice for you.

Features:

- IP 20
- Cat.5
- narrow design enables side-by-side mounting on the patch panel

General ordering data

Version	Cable splitter module, IP20
Order No.	3095680000
Type	IE-AD-3RJ12-1:1
GTIN (EAN)	4099987117050
Qty.	10 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 37 g

Temperatures

Storage temperature Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

General data

Connection 1	RJ12	Connection 2	RJ12
Colour	black	Housing main material	PBT, UL 94: V-0
Contact surface	Gold over nickel	Shielding	unshielded
Protection degree	IP20	Plugging cycles	750

Electrical properties

Insulation resistance 1000 MΩ at 500 V DC Nominal voltage 125 V

General standards

Connector standard TIA-1096-A

Classifications

ETIM 8.0	EC000313	ETIM 9.0	EC000313
ETIM 10.0	EC000313	ECLASS 14.0	27-44-03-20
ECLASS 15.0	27-44-03-20		

Drawings

