

IE-AD-3RJ12-1:1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



If you need an adapter that lets you use one 8-core installation cable for two 4-core services, then the Weidmüller cable splitter module is the right choice for you.

Features:

- IP 20
- Cat.5
- narrow design enables side-by-side mounting on the patch panel

General ordering data

| | |
|------------|-----------------------------|
| Version | Cable splitter module, IP20 |
| Order No. | 3095680000 |
| Type | IE-AD-3RJ12-1:1 |
| GTIN (EAN) | 4099987117050 |
| Qty. | 10 items |

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 37 g

Temperatures

Storage temperature Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-------------------|------------------|-----------------------|-----------------|
| Connection 1 | RJ12 | Connection 2 | RJ12 |
| Colour | black | Housing main material | PBT, UL 94: V-0 |
| Contact surface | Gold over nickel | Shielding | unshielded |
| Protection degree | IP20 | Plugging cycles | 750 |

Electrical properties

Insulation resistance 1000 MΩ at 500 V DC Nominal voltage 125 V

General standards

Connector standard TIA-1096-A

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000313 | ETIM 9.0 | EC000313 |
| ETIM 10.0 | EC000313 | ECLASS 14.0 | 27-44-03-20 |
| ECLASS 15.0 | 27-44-03-20 | | |

Drawings

