

VPU PV EXTENDER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Extensive accessories round off the product range

General ordering data

Order No.	3123510000
Type	VPU PV EXTENDER
GTIN (EAN)	4099987270199
Qty.	9 items

VPU PV EXTENDER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	1.78 g
------------	--------

Temperatures

Storage temperature	Operating temperature
---------------------	-----------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Insulation coordination acc. to EN 50178

Surge voltage category	III	Pollution severity	2
------------------------	-----	--------------------	---

Rated data IEC / EN

Rated voltage (DC)	1500 V	Voltage type	DC
--------------------	--------	--------------	----

Connection data

Wire connection method	Screw connection	Type of connection	Screw connection
Tightening torque, min.	1.2 Nm	Tightening torque, max.	4.5 Nm
Clamping range, rated connection	10 mm ²	Clamping range, min.	1.5 mm ²
Clamping range, max.	16 mm ²	Wire cross-section, solid, min.	1.5 mm ²
Wire cross-section, solid, max.	16 mm ²	Wire connection cross section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded, max.	16 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	1.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	10 mm ²	Connection cross-section, stranded, min.	1.5 mm ²
Connection cross-section, stranded, max.	25 mm ²		

Electrical data

Voltage type	DC	Nominal current	63 A
--------------	----	-----------------	------

Classifications

ETIM 8.0	EC002496	ETIM 9.0	EC002496
ETIM 10.0	EC002496	ECLASS 14.0	27-17-14-92
ECLASS 15.0	27-17-14-92		