

VPU PV EXTENDER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Extensive accessories round off the product range

General ordering data

Order No.	3123510000
Type	VPU PV EXTENDER
GTIN (EAN)	4099987270199
Qty.	9 items

VPU PV EXTENDER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 1.78 g

Temperatures

Storage temperature Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Insulation coordination acc. to EN 50178

Surge voltage category III Pollution severity 2

Rated data IEC / EN

Rated voltage (DC) 1500 V

Connection data

Wire connection method	Screw connection	Type of connection	Screw connection
Tightening torque, min.	1.2 Nm	Tightening torque, max.	4.5 Nm
Clamping range, rated connection	10 mm ²	Clamping range, min.	1.5 mm ²
Clamping range, max.	16 mm ²	Wire cross-section, solid, min.	1.5 mm ²
Wire cross-section, solid, max.	16 mm ²	Wire connection cross section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded, max.	16 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	1.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	10 mm ²	Connection cross-section, stranded, min.	1.5 mm ²
Connection cross-section, stranded, max.	16 mm ²		

Electrical data

Nominal current 63 A

Classifications

ETIM 8.0	EC001457	ETIM 9.0	EC001457
ETIM 10.0	EC001457	ECLASS 14.0	27-17-14-03
ECLASS 15.0	27-17-14-03		