

## DC SB M 50A 2POL EVO 1KV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Photovoltaics, Switch, Switch disconnecter, 1000 V, DC version, 50 A, Manual switch
Order No.	<a href="#">3123790000</a>
Type	DC SB M 50A 2POL EVO 1KV
GTIN (EAN)	4099987272001
Qty.	1 items

## DC SB M 50A 2POL EVO 1KV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	121.5 mm	Depth (inches)	4.7835 inch
Height	165 mm	Height (inches)	6.4961 inch
Width	140 mm	Width (inches)	5.5118 inch
Net weight	704 g		

### Temperatures

Ambient temperature	-30 °C...50 °C
---------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Protection degree	IP65
-------------------	------

### Classifications

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

### Tender specification sheets

Long specification	<p>Load break switch in polyester housing.                  Suitable for switching off the DC side.                  Number of poles: 2                  Operating current, rated value (Ie):</p> <ul style="list-style-type: none"> <li>- according to IEC (PV1, 1000 V): 50 A</li> <li>- according to IEC (PV1, 1500 V): 20 A</li> <li>- according to IEC (PV2, 1000 V): 20 A</li> <li>- according to IEC (PV2, 1500 V): 8 A</li> </ul> <p>Rated insulation voltage (Ui):</p> <ul style="list-style-type: none"> <li>- according to IEC: 1500 V</li> </ul> <p>Suitability for use:                  Main switch: Yes                  Number of contacts normally open: 2                  Number of contacts normally closed: 0                  Number of switching positions: 2                  Lockable: Yes                  The switch is mounted using 4 screws.</p>
--------------------	--

### DC SB M 50A 2POL EVO 1KV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Technical data

[www.weidmueller.com](http://www.weidmueller.com)

Protection class (IP): 65  
Polyester housing with  
connection via MC4-Evo  
2 connector, compatible  
with cable type TÜV 2  
Pfg 1169/08.07 / EN  
50618:2063  
Dimensions HxWxD:  
235x140x12.5 mm.  
Approval according to low  
voltage switchgear and  
controlgear IEC 60947-3,  
DIN VDE 0660 Part 107  
(EN 60947-3)

DC SB M 50A 2POL EVO 1KV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

