Data sheet

CC-FO 30/60 MM LF RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Standard included: CC
Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.
Your benefits with MultiMark
- “Different materials for various requirements“
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Order No.	3128410000
Type	CC-FO 30/60 MM LF RT
GTIN (EAN)	4099987301763
Qty.	500 items

Data sheet

CC-FO 30/60 MM LF RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	0.55 mm	Depth (inches)	0.0217 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	60 mm	Width (inches)	2.3622 inch
Net weight	1.55 g		

General data

Adhesive	PE-foam with acrylic adhesive	Version	Self-adhesive, halogen-free
Width	60 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Colour	yellow, red	Halogen	No
Basic material	Polyester	Printed characters	without
Size of labelling field	30 x 60 mm	Approval acc. to UL 969	Yes
Number per roll	100		

Device markers

Halogen	No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		