

**HDC MDU 2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Version	Module, 0 V, 0 A, Number of poles: 0, without, Male, Female, Required plug-in slots: 1
Order No.	<a href="#">3149600000</a>
Type	HDC MDU 2
GTIN (EAN)	409998759878 1
Qty.	5 items

## HDC MDU 2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	34.1 mm	Depth (inches)	1.3425 inch
Height	16.8 mm	Height (inches)	0.6614 inch
Width	34.1 mm	Width (inches)	1.3425 inch
Length	14.6 mm	Length (inches)	0.5748 inch
Net weight	1 g		

### Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Number of poles	0	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	Male, Female
Pollution severity	3	Basic material	Polycarbonate, glass fibre reinforced
Series	ModuPlug	Rated voltage (DIN EN 61984)	0 V
Rated current (DIN EN 61984)	0 A	Required plug-in slots	1

### Version

Type of connection	without	Conductor cross-section, max.	0 mm <sup>2</sup>
Conductor cross-section, min.	0 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-17
ECLASS 15.0	27-44-02-17		

Drawings

