

**CB 160/4,8 TR NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Order No.	3155780000
Type	<a href="#">CB 160/4,8 TR NC</a>
GTIN (EAN)	4099987656870
Qty.	100 items

**CB 160/4,8 TR NC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	160 mm	Depth (inches)	6.2992 inch
Height	0 mm	Width	4.8 mm
Width (inches)	0.189 inch	Net weight	1.02 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Installation materials**

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Polyamide 66	Tensile strength	220 N
Bundle diameter, max.	39 mm	Tensile strength (Pound-force)	49 lbf
Bundle diameter, min.	3 mm		

**Classifications**

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		