


CB 250/7,6 TR NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	3155860000
Type	CB 250/7,6 TR NC
GTIN (EAN)	4099987657099
Qty.	100 items

CB 250/7,6 TR NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0 mm	Height	250 mm
Height (inches)	9.8425 inch	Width	7.6 mm
Width (inches)	0.2992 inch	Net weight	3.55 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Polyamide 66	Tensile strength	550 N
Bundle diameter, max.	63 mm	Tensile strength (Pound-force)	124 lbf
Bundle diameter, min.	4 mm		

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		