

**CB 760/9 TR NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



**General ordering data**

Order No.	3156020000
Type	<a href="#">CB 760/9 TR NC</a>
GTIN (EAN)	4099987657631
Qty.	100 items

## CB 760/9 TR NC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0 mm	Height	760 mm
Height (inches)	29.9212 inch	Width	9 mm
Width (inches)	0.3543 inch	Net weight	13.1 g

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Polyamide 66	Tensile strength	800 N
Bundle diameter, max.	225 mm	Tensile strength (Pound-force)	180 lbf
Bundle diameter, min.	10 mm		

## Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		