

CB 180/4,6 TR BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	3156100000
Type	CB 180/4,6 TR BK
GTIN (EAN)	4099987657891
Qty.	100 items

CB 180/4,6 TR BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0 mm	Height	180 mm
Height (inches)	7.0866 inch	Width	4.6 mm
Width (inches)	0.1811 inch	Net weight	1.08 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Basic material	Polyamide 66	Tensile strength	220 N
Bundle diameter, max.	42 mm	Tensile strength (Pound-force)	49 lbf
Bundle diameter, min.	3 mm		

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		