

CB 750/7,6 TR BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|----------------------------------|
| Order No. | 3156290000 |
| Type | CB 750/7,6 TR BK |
| GTIN (EAN) | 4099987658508 |
| Qty. | 100 items |

CB 750/7,6 TR BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|-----------------|--------------|------------|---------|
| Depth | 0 mm | Height | 750 mm |
| Height (inches) | 29.5275 inch | Width | 7.6 mm |
| Width (inches) | 0.2992 inch | Net weight | 10.13 g |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Installation materials

| | | | |
|-----------------------------------|--------------|-----------------------------------|---------|
| UV-resistant | No | For re-opening | No |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 85 °C |
| Operating temperature range, min. | -40 °C | Halogen | No |
| Basic material | Polyamide 66 | Tensile strength | 550 N |
| Bundle diameter, max. | 220 mm | Tensile strength (Pound-force) | 124 lbf |
| Bundle diameter, min. | 4 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |