

## FUSE WSFL 10X85 32A 1K5V GPV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



gPV 10×85 cylindrical fuse cartridges are designed to provide compact, safe and economical protection of photovoltaic modules (field protection) with voltages up to 1,500 DC. They provide protection against both overload and short circuit (gPV class according to the requirements of IEC60269-6 and UL248-19 standards).

### General ordering data

Version	Photovoltaics, Cartridge fuse, 1500 V, 10x85, gPV, 32 A
Order No.	<a href="#">4000002612</a>
Type	FUSE WSFL 10X85 32A 1K5V GPV
GTIN (EAN)	8430243419659
Qty.	5 items

**FUSE WSFL 10X85 32A 1K5V GPV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	85 mm	Height (inches)	3.3464 inch
Width	10.3 mm	Width (inches)	0.4055 inch
Net weight	5 g		

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Fuse cartridge**

Fuse-link standard	IEC 60269-1, gPV (EN 60269-6)	Current	32 A
Rated DC voltage	1500 V	Rated breaking capacity	50 kA
Material of contacts	silver-plated	Power dissipation, max.	7.4 W

**Classifications**

ETIM 8.0	EC002704	ETIM 9.0	EC002704
ETIM 10.0	EC002704	ECLASS 14.0	27-14-20-02
ECLASS 15.0	27-14-20-02		