

PTSC KB40X14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

General ordering data

Version	Mounting screw (Terminal), 0.00 mm, Steel, Depth: 7 mm, Width: 16.9 mm, Height: 7 mm
Order No.	4019420000
Type	PTSC KB40X14
GTIN (EAN)	4008 190243029
Qty.	100 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	7 mm	Depth (inches)	0.2756 inch
Height	7 mm	Height (inches)	0.2756 inch
Width	16.9 mm	Width (inches)	0.6654 inch
Net weight	1.13 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Surface finish Miscellaneous Basic material Steel

General data

Colour grey Colour chart (similar) RAL 7035

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		