PCF CROSSLINK 10MM PITCH



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com



Large potential for small terminals.

For efficient electrical distribution directly at the connection:

- Isolated comb rail
- Available with the most standard pole numbers
- Easy to shorten

Simply reduce in size to match the number of poles and connect with the conductor in a single working procedure.

For retrofitting or deliberate reduction of the thermal load on the PCB.

General ordering data

Version	Printed circuit board terminals, Accessories, Cross- connector, Number of poles: 2	
Order No.	<u>6382690000</u>	
Туре	PCF CROSSLINK 10MM PITCH	
GTIN (EAN)	4008190549558	
Qty.	1000 items	
Product data		
Packaging	Вох	

Catalogue status / Drawings



PCF CROSSLINK 10MM PITCH



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Conform				
1 10				
oliance				
Compliant without exemption				
No SVHC above 0.1 wt%				
10.00 mm	Pitch in inches (P)	0.394 "		
2	Pin series quantity	1		
0.394 "	Protection degree	IP20		
		,		
Cu-allov	Storage temperature, min	-40 °C		
,		-50 °C		
		-25 °C		
100 °C	remperature range, matanation, min.	20 0		
ection				
ection				
Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P)				
IEC 60664-1, IEC 61984				
n	VDF I II	045.00		
		215.00 mm 55.00 mm		
137.00 mm	VPE neight	55.00 mm		
recognized standards and no fulfill decorative properties in	orms and comply with the assured proper n accordance with IPC-A-610 "Class 2". F	rties in the data sheet resp		
 Long term storage of the p 70%, 36 months 	product with average temperature of 50 °	C and maximum humidity		
EC002848	ETIM 7.0	EC002848		
	1.13 g Dliance Compliant without exemption No SVHC above 0.1 wt% 10.00 mm 2 0.394 " Cu-alloy 70 °C 100 °C 100 °C ection Length of ferrules is to be chosen depending on the product and the rated voltage., The outside diameter of the plastic collar should not be larger than the pitch (P) IEC 60664-1, IEC 61984 Box 137.00 mm Conformity: The products are recognized standards and not fulfill decorative properties in can be evaluated on request • Long term storage of the products are recognized.	1.13 g Diliance		

Creation date 05.11.2025 11:08:11 MEZ

Catalogue status / Drawings 2







Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

ETIM 10.0	EC002848	ECLASS 9.0	27-44-04-92
ECLASS 9.1	27-44-04-92	ECLASS 10.0	27-44-04-92
ECLASS 11.0	27-46-04-06	ECLASS 12.0	27-46-04-06
ECLASS 13.0	27-46-04-06	ECLASS 14.0	27-46-04-06
ECLASS 15.0	27-46-04-06		