

RS PLC IPC-620 12-POINTS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Point-to-point connection**

- Conversion between the IPC-620 connector to plug-in connector
- 12-22-24-34-38 points

General ordering data

Order No.	6720000787
Type	RS PLC IPC-620 12-POINTS
GTIN (EAN)	4050118485790
Qty.	1 items

RS PLC IPC-620 12-POINTS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	61 mm	Depth (inches)	2.4016 inch
Height	266 mm	Height (inches)	10.4724 inch
Width	29 mm	Width (inches)	1.1417 inch
Net weight	8001.53 g		

Temperatures

Storage temperature	0...50 °C	Operating temperature	0...50 °C
---------------------	-----------	-----------------------	-----------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	3820ceea-2b49-4a61-bda5-08f3867b3419

Connection data

Number of poles (control side)	12-pole	Connection (field side)	Card edge
Connection on control side	3.5 pitch S2L header		

Connection data

Connection (field side)	Card edge
-------------------------	-----------

Ratings data

Operating voltage	150 V	Max. current per channel	5 A
-------------------	-------	--------------------------	-----

Insulation coordination (EN50178)

Pollution severity level	2
--------------------------	---

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

