

## RS PLC IPC-620 22-POINTS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Point-to-point connection

- Conversion between the IPC-620 connector to plug-in connector
- 12-22-24-34-38 points

### General ordering data

Order No.	6720000788
Type	<a href="#">RS PLC IPC-620 22-POINTS</a>
GTIN (EAN)	4050118485806
Qty.	1 items

## RS PLC IPC-620 22-POINTS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	61 mm	Depth (inches)	2.4016 inch
Height	266 mm	Height (inches)	10.4724 inch
Width	29 mm	Width (inches)	1.1417 inch
Net weight	1013.24 g		

## Temperatures

Storage temperature	0...50 °C	Operating temperature	0...50 °C
---------------------	-----------	-----------------------	-----------

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	3820ceea-2b49-4a61-bda5-08f3867b3419

## Connection data

Number of poles (control side)	22-pole	Connection (field side)	Card edge
Connection on control side	3.5 pitch S2L header		

## Connection data

Connection (field side)	Card edge
-------------------------	-----------

## Ratings data

Operating voltage	150 V	Max. current per channel	5 A
-------------------	-------	--------------------------	-----

## Insulation coordination (EN50178)

Pollution severity level	2
--------------------------	---

## Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

RS PLC IPC-620 22-POINTS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

