

## RS PLC IPC-620 38-POINTS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Point-to-point connection

- Conversion between the IPC-620 connector to plug-in connector
- 12-22-24-34-38 points

### General ordering data

Order No.	6720001225
Type	<a href="#">RS PLC IPC-620 38-POINTS</a>
GTIN (EAN)	4050118485813
Qty.	1 items

**RS PLC IPC-620 38-POINTS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	126 mm	Depth (inches)	4.9606 inch
Height	266 mm	Height (inches)	10.4724 inch
Width	29 mm	Width (inches)	1.1417 inch
Net weight	6000 g		

**Temperatures**

Storage temperature 0...50 °C      Operating temperature 0...50 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	3820ceea-2b49-4a61-bda5-08f3867b3419

**Connection data**

Number of poles (control side)	20-pole	Connection (field side)	Card edge
Connection on control side	SL 5.08		

**Connection data**

Connection (field side) Card edge

**Ratings data**

Operating voltage	125 V	Max. current per channel	3 A
Total operating current	10 A		

**Insulation coordination (EN50178)**

Pollution severity level 2

**Classifications**

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

RS PLC IPC-620 38-POINTS

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

