

**RIM 2 110/230VDC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

Similar to illustration

Pluggable protective modules for the D-SERIES relay sockets, with optional protective functions.

- With green LED and free-wheeling diode

**General ordering data**

Version	D-SERIES, LED module with freewheel diode, Rated control voltage: 110...230 V DC, Plug-in connection
Order No.	<a href="#">7760056017</a>
Type	RIM 2 110/230VDC
GTIN (EAN)	4032248896615
Qty.	10 items

## RIM 2 110/230VDC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E312083

## Dimensions and weights

Depth	32 mm	Depth (inches)	1.2598 inch
Height	8.6 mm	Height (inches)	0.3386 inch
Width	12.4 mm	Width (inches)	0.4882 inch
Net weight	2.1 g		

## Temperatures

Storage temperature Operating temperature

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Rated data UL

Certificate No. (cURus) E312083

## Control side

Rated control voltage 110...230 V DC Status indicator Green LED

Protective circuit Free-wheeling diode

## General data

Colour black

UL94 flammability rating component	Component	Housing
	UL94 flammability rating	V-2

## Further details of approvals / standards

Certificate No. (CSA) 80107692 Certificate No. (cURus) E312083

## Connection data

Wire connection method Plug-in connection

## Classifications

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		


**RIM 2 110/230VDC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Wiring diagram**



**Dimensional drawing**

