

## PAC-UNIV-RV36-F-2M5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

### General ordering data

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789106025</a>                                 |
| Type       | PAC-UNIV-RV36-F-2M5  |
| GTIN (EAN) | 8430243960090  |
| Qty.       | 1 items  |

## PAC-UNIV-RV36-F-2M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 489.5 g |
|------------|---------|

### Temperatures

|                     |             |                       |          |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

### Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

### General Data

|                     |                             |                       |   |
|---------------------|-----------------------------|-----------------------|---|
| Cable length        | 2.5 m                       | Suitable for          | Digital signals                             |
| Basic material      | PVC                         | Cable                 | Cable LiYY                                  |
| Interface connector | WEIDMUELLER RSV 36P<br>MALE | Number of poles, min. | 36-pole                                     |
| Outer diameter      | 11.2 ± 1 mm                 | Connector PLC side    | H0.25/10 (FERRULES<br>0.25mm <sup>2</sup> ) |
| Wire cross-section  | 0.25 mm <sup>2</sup>        |                       |   |

### Electrical Data

|   |           |                       |                     |
|---|-----------|-----------------------|---------------------|
| Total current, max.                         | 3 A       | High voltage test     | 1 KV/1s             |
| Permissible current strength per path, max. | 1 A       | Rated voltage         | ≤ 250 Vdc ≤ 250 Vac |
| Resistance                                  | ≤ 80 mΩ/m | Capacity wire / wires | 300 pF/m            |
| Capacity wire / shield                      | 300 pF/m  |                       |                     |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |