

**PAC-MIMQ-SD37-V0-2M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789682025</a>                                 |
| Type       | PAC-MIMQ-SD37-V0-2M5                                       |
| GTIN (EAN) | 4032248201600  |
| Qty.       | 1 items  |

**PAC-MIMQ-SD37-V0-2M5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 634 g

**Temperatures**

Storage temperature -10...60 °C Operating temperature -10...50

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

|                     |                                  |                       |                  |
|---------------------|----------------------------------|-----------------------|------------------|
| Cable length        | 2.5 m                            | Suitable for          | Analogue signals |
| Basic material      | PVC                              | Cable                 | Cable LiYY       |
| Interface connector | 2X FLAT CABLE CONNECTOR HE10 20P | Number of poles, min. | 20-pole          |
| Outer diameter      | 8.6 ± 1 mm                       | Connector PLC side    | SUB-D FEMALE 37P |
| Wire cross-section  | 0.25 mm <sup>2</sup>             |                       |                  |

**Electrical Data**

|   |           |                   |                     |
|---|-----------|-------------------|---------------------|
| Total current, max.                         | 3 A       | High voltage test | 1 KV/1s             |
| Permissible current strength per path, max. | 1 A       | Rated voltage     | ≤ 60 V DC ≤ 25 V AC |
| Resistance                                  | ≤ 80 mΩ/m |                   |                     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |