

PAC-CMLX-HE20-V3-0M5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

| | |
|------------|------------------------------------------------------------|
| Version | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm ² |
| Order No. | 7789695005 |
| Type | PAC-CMLX-HE20-V3-0M5 |
| GTIN (EAN) | 4032248246342 |
| Qty. | 1 items |

PAC-CMLX-HE20-V3-0M5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|-------|
| Net weight | 131 g |
|------------|-------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|----------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 |
|---------------------|-------------|-----------------------|----------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

General Data

| | | | |
|---------------------|---------------------------------|-----------------------|-----------------------------------------|
| Cable length | 0.5 m | Suitable for | Digital signals |
| Basic material | PVC | Cable | Cable LiYY |
| Interface connector | FLAT CABLE CONECTOR HE10 20P | Number of poles, min. | 20-pole |
| Outer diameter | 8.6 ± 1 mm | Connector PLC side | ROCKWELL COMPACT LOGIX 1769-RTBN 18P |
| Wire cross-section | 0.25 mm ² | | |

Electrical Data

| | | | |
|---------------------------------------------|-----------|-----------------------|-------------------|
| Total current, max. | 3 A | High voltage test | 1 KV/1s |
| Permissible current strength per path, max. | 1 A | Rated voltage | ≤ 60 Vdc ≤ 25 Vac |
| Resistance | ≤ 80 mΩ/m | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |