

## CB 135/2,5 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

### General ordering data

Version	Cable ties, 2.5 x 135 mm, Polyamide 66, 80 N
Order No.	<a href="#">7940006047</a>
Type	CB 135/2,5 BK
GTIN (EAN)	403224852009 1
Qty.	15000 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E317499

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	135 mm	Height (inches)	5.3149 inch
Width	2.5 mm	Width (inches)	0.0984 inch
Net weight	0.38 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	32 mm	Basic material	Polyamide 66
Tensile strength	80 N	Bundle diameter, max.	32 mm
Tensile strength (Pound-force)	18 lbf	Bundle diameter, min.	1 mm

Important note

Product information	Number of bags in box (pieces): 150 Number of items in bag (pieces): 100 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	---

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

