



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

### General ordering data

|            |   |
|------------|---|
| Version    | Cable ties, 7.5 x 300 mm, Polyamide 66, 540 N |
| Order No.  | <a href="#">7940006068</a>                    |
| Type       | CB 300/7,5 NC                                 |
| GTIN (EAN) | 4032248520213                                 |
| Qty.       | 100 items                                     |

## Technical data

### Approvals

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E317499                    |

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 1.7 mm | Depth (inches)  | 0.0669 inch |
| Height     | 300 mm | Height (inches) | 11.811 inch |
| Width      | 7.5 mm | Width (inches)  | 0.2953 inch |
| Net weight | 4.3 g  |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...85 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Installation materials

|                                   |         |                                   |              |
|-----------------------------------|---------|-----------------------------------|--------------|
| UV-resistant                      | No      | For re-opening                    | No           |
| UL 94 flammability rating         | V-2     | Operating temperature range, max. | 85 °C        |
| Operating temperature range, min. | -40 °C  | Halogen                           | No           |
| Cable diameter, max.              | 80 mm   | Basic material                    | Polyamide 66 |
| Tensile strength                  | 540 N   | Bundle diameter, max.             | 80 mm        |
| Tensile strength (Pound-force)    | 121 lbf | Bundle diameter, min.             | 4 mm         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000046    | ETIM 9.0    | EC000046    |
| ETIM 10.0   | EC000046    | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 |             |             |

**Drawings**

