

## CB 500/12,5 NC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

### General ordering data

Version	Cable ties, 12.5 x 500 mm, Polyamide 66, 1080 N
Order No.	<a href="#">7940006078</a>
Type	CB 500/12,5 NC
GTIN (EAN)	4032248520299
Qty.	500 items

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E317499

**Dimensions and weights**

Depth	1.95 mm	Depth (inches)	0.0768 inch
Height	500 mm	Height (inches)	19.685 inch
Width	12.5 mm	Width (inches)	0.4921 inch
Net weight	14.2 g		

**Temperatures**

Operating temperature range	-40...85 °C
-----------------------------	-------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Installation materials**

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	143 mm	Basic material	Polyamide 66
Tensile strength	1080 N	Bundle diameter, max.	143 mm
Tensile strength (Pound-force)	243 lbf	Bundle diameter, min.	30 mm

**Important note**

Product information	Number of bags in box (pieces): 10 Number of items in bag (pieces): 50 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

**Classifications**

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

