

CB 1000/12,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 12.5 x 1000 mm, Polyamide 66, 1080 N
Order No.	7940006085
Type	CB 1000/12,5 BK
GTIN (EAN)	4032248520343
Qty.	500 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	1000 mm	Height (inches)	39.37 inch
Width	12.5 mm	Width (inches)	0.4921 inch
Net weight	24.3 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	302 mm	Basic material	Polyamide 66
Tensile strength	1080 N	Bundle diameter, max.	302 mm
Tensile strength (Pound-force)	243 lbf	Bundle diameter, min.	40 mm

Important note

Product information	Number of bags in box (pieces): 10 Number of items in bag (pieces): 50 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.
---------------------	---

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

