

IE-FC-SET-SP-US-D010-KN-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom
Order No.	7940111830
Type	IE-FC-SET-SP-US-D010-KN-M
GTIN (EAN)	4064675115694
Qty.	1 items

IE-FC-SET-SP-US-D010-KN-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	999 g
------------	-------

Temperatures

Storage temperature	Operating temperature
Installation temperature	

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General data

Protection degree	IP65, in closed state	Protection class (UL)	Type 12
Reference product	IE-FC-DFM-KNOB , IE-FC-DSP-CI/3A/2ST/1D9 , IE-FCI-PWCB-3A , IE-BI-RJ45-C		

Technical data

Insert plate	2x data, 1x signal, 1x fuse, 1x GFCI, Shielded	Frame	Metal cover
Rated voltage for socket	125 V	Data inserts	RJ45 coupling Cat.6A
Rated current for socket	20 A		

Important note

Product information	All components in this set have UL approval. For more details please check the reference products that are included in the kit.
---------------------	---

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		