

FAD 1771-WA/WC SL10 M US

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Adapters for migration – PLC-5.

The front adapters with pre-assembled cables provide a safe migration from the PLC-5 cards to other PLC/DCS systems or the u-remote modules from Weidmüller.

General ordering data

Order No.	7940125447
Type	FAD 1771-WA/WC SL10 M US
GTIN (EAN)	4064675209072
Qty.	1 items

FAD 1771-WA/WC SL10 M US

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Depth	53 mm	Depth (inches)	2.0866 inch
Height	269 mm	Height (inches)	10.5905 inch
Width	32 mm	Width (inches)	1.2598 inch
Net weight	13214.52 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Number of poles (control side)	10-pole	Connection (field side)	Card edge
Connection on control side	SL 3.5 header		

Connection data

Connection (field side)	Card edge	Connection to PLC	SL 3.5/F 10p connector
-------------------------	-----------	-------------------	------------------------

Ratings data

Max. current per channel	2 A	Total operating current	6 A
--------------------------	-----	-------------------------	-----

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 300 V AC
Surge voltage category	II	Pollution severity level	2
Insulation test voltage AC	1.2 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

FAD 1771-WA/WC SL10 M US

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

