

FPL 4G2.5/Q8KW/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Plastic housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, PVC, Cross-section: 2.5 mm ² , 3 m
Order No.	8000011742
Type	FPL 4G2.5/Q8KW/3
GTIN (EAN)	4050118190403
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	7.5 mm	Length (inches)	0.2953 inch
Diameter	8.9 mm	Net weight	550 g

Temperatures

Storage temperature	Operating temperature
---------------------	-----------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

Classifications

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

FPL 4G2.5/Q8KW/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Pin assignments

	Pin	Conductor	Assignment
8 = nc	1	1	U
	2	-	-
5 = nc	3	3	W
	4	-	-
⊕ = PE	5	-	-
	6	-	-
3 = W	7	2	V
	8	-	-
2 = nc	PE	gr./yell.	PE