

## FPL 7G2.5C/Q8MW/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

### General ordering data

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Classic 110 CY 7G2.5 or similar, PVC, Cross-section: 2.5 mm <sup>2</sup> , 3 m
Order No.	<a href="#">8000011751</a>
Type	FPL 7G2.5C/Q8MW/3
GTIN (EAN)	4050118190434
Qty.	1 items

**FPL 7G2.5C/Q8MW/3**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	7.5 mm	Length (inches)	0.2953 inch
Diameter	8.9 mm	Net weight	1349 g

**Temperatures**

Storage temperature	Operating temperature
Limit temperature	-40 °C ... 80 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

**Classifications**

ETIM 8.0	EC001576	ETIM 9.0	EC001576
ETIM 10.0	EC001576	ECLASS 14.0	27-06-04-02
ECLASS 15.0	27-06-04-02		

## FPL 7G2.5C/Q8MW/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

### Pin assignments

	Pin	Conductor	Assignment
8 = nc	1	1	U
5 = nc	2	-	-
⊕ = PE	3	3	W
3 = W	4	4	Brake
2 = nc	5	-	-
	6	5	Brake
	7	2	V
	8	-	-
	PE	gr./yell.	PE