

**TS35X7.5 ST FPC 20 VER**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**



Similar to illustration

Accessories

**General ordering data**

|            |  |
|------------|--|
| Version    | Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel, galvanized, chromium-plated |
| Order No.  | <a href="#">8000037558</a>   |
| Type       | TS35X7.5 ST FPC 20 VER   |
| GTIN (EAN) | 4050118653229  |
| Qty.       | 20 items   |

**TS35X7.5 ST FPC 20 VER**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 7.5 mm | Depth (inches)  | 0.2953 inch |
| Height     | 35 mm  | Height (inches) | 1.378 inch  |
| Width      | 165 mm | Width (inches)  | 6.4961 inch |
| Net weight | 60 g   |                 |             |

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

|                    |              |                     |                             |
|--------------------|--------------|---------------------|-----------------------------|
| Material thickness | 1 mm         | Installation advice | Direct mounting             |
| Standards          | DIN EN 60715 | Surface finish      | galvanized, chromium-plated |
| Basic material     | Steel        | Integral fixing     | Screwed                     |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ETIM 10.0   | EC001285    | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 |             |             |