

**TS 35X105\_MPC\_12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**



Similar to illustration

Accessories

**General ordering data**

Version	Rail, TS 35 x 7.5, TS 35, Width: 164 mm, without slot, Steel, galvanic zinc plated and passivated
Order No.	<a href="#">8000037603</a>
Type	TS 35X105_MPC_12
GTIN (EAN)	4050118653151
Qty.	20 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	164 mm	Width (inches)	6.4567 inch
Length	105 mm	Length (inches)	4.1338 inch
Net weight	1.7 g		

**Temperatures**

Operating temperature
-----------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Material thickness	1 mm	Installation advice	2 screws
Standards	DIN EN 60715	Surface finish	galvanic zinc plated and passivated
Basic material	Steel	Integral fixing	Screwed

**Classifications**

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		