Data sheet

TS35 MPC 1717 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

Version	Rail, TS 35 x 7.5, TS 35, Width: 106 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037605
Type	TS35 MPC 1717 VER
GTIN (EAN)	4050118653175
Qty.	20 items

TS35 MPC 1717 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	106 mm	Width (inches)	4.1732 inch
Net weight	21.73 g		

Temperatures

Operating temperature	

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Installation advice	Direct mounting	Standards	DIN EN 60715
Surface finish	galvanized, chromium-plated	Basic material	Steel
Integral fixing	Screwed		

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		